## Rittal – The System.

Faster – better – everywhere.





# AE 1018.600 Wall-mounted AE

State: 12/14/2025 (Source: rittal.com/us-en)



## AE 1018.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

#### **Features**

Model No.	AE 1018.600
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 µm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s)
	Mounting panel
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 12
Protection category IP to EN 60 529	IP 55
IK code	IK08
Dimensions	Width: 1,000 mm
	Height: 1,000 mm
	Depth: 300 mm
	Width: 39.4 "
	Height: 39.4 ″
	Depth: 11.8 "
Dimensions of mounting plate (W	939 mm x 955 mm
x H)	37 ″ x 37.6 ″
Number of doors	2
No. of locks	2

© Rittal 2025

## Features

Lock	Lock version: Cam	
	No. of locks: 2	
	Lock Insert: 3 mm double-bit	
	Material lock: Die-cast zinc, nickel-plated	
Base material	Stainless steel 1.4301 (AISI 304)	
Packaging unit	1 pc(s).	
Net weight	65.4	
Gross weight	67	
Customs tariff number	94032080	
EAN	4028177000650	
E-Number Sweden	E3404428	
ETIM 9	EC000261	
ETIM 8	EC000261	
ECLASS 8.0	27180101	

## Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3