

Rittal – The System.

Faster – better – everywhere.



AX 1058.000

Basic enclosure AX, carbon steel

State: 6/14/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1058.000 - Basic enclosure AX, carbon steel

The AX wall-mounted enclosure with embossed enclosure cams in the roof, base and side replicates the familiar 25 mm system grid from the VX25 large enclosure. Thanks to this unique, patented system, AX wall-mounted control enclosures are prepared for all expansion and retrofit cases. System components and accessories can be installed and retrofitted easily, quickly and safely on rails without drilling.



Features

| | |
|----------------|--|
| Model No. | AX 1058.000 |
| Benefits | <p>More interior finishing options thanks to integrated housing cams in the 25 mm system grid in combination with the rail for interior finishing and our wide range of system accessories</p> <p>Maintaining the protection class (UL approval) by mounting the rail for interior installation without drilling</p> <p>Additional mounting level and increased load capacity due to base configuration rail</p> <p>Easy planning and configuration with the Rittal configurator RiPanel</p> |
| Material | <p>Housing: Carbon steel</p> <p>Door: Carbon steel, all-round foamed-in PU seal</p> |
| Surface finish | <p>Housing and door: Dipcoat primed, powder-coated on the outside, textured paint</p> <p>Mounting panel: Zinc-plated</p> |
| Color | RAL 7035 |

Features

| | |
|--------------------------------------|--|
| Supply includes | Housing with door(s) Flange (gland) plate(s) in enclosure base Mounting panel Punched door strip Lock: 3 mm double-bit |
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 4 NEMA 12 |
| Protection category IP to EN 60529 | IP 66 |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 12 |
| IK code | IK10 |
| Dimensions | Width: 600 mm Height: 800 mm Depth: 250 mm Width: 23.6 " Height: 31.5 " Depth: 9.84 " |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 1.5 mm 0.06 " |
| Material thickness – mounting plate | 2.5 mm 0.1 " |
| Dimensions of mounting plate (W x H) | 545 mm x 775 mm 21.5 " x 30.5 " |
| Number of doors | 1 |
| Interchangeable door catch | Yes |
| No. of locks | 2 |

Features

| | |
|-------------------------------------|--|
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit |
| Gland plate | Size: 4 Qty.: 1 |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 30.25 kg |
| Gross weight | 32 kg |
| PCF/VE (cradle-to-gate) | 116.31 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | AX wall-mounted enclosure, WHD: 600x800x250 mm, carbon steel, with mounting panel, single-door, with two cam locks |

Approvals

| | |
|--------------|--|
| Approvals | Bureau Veritas DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Manufacturer's declaration Declaration of conformity Declaration of conformity UK PCF-declaration |
