## Rittal – The System.

Faster – better – everywhere.





# WM 1077.250 WM wall-mounted enclosure

State: 12/14/2025 (Source: rittal.com/us-en)



### WM 1077.250 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.







#### **Features**

| Model No.                       | WM 1077.250  |
|---------------------------------|--|
| Material                        | Door: Carbon steel, all-round foamed-in PU seal<br>Housing: Carbon steel       |
| Surface finish                  | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint |
|                                 | Mounting panel: Zinc-plated  |
| Color                           | RAL 7035   |
| Supply includes                 | Housing with door(s)   |
|                                 | Door hinged on left  |
|                                 | Mounting plate   |
|                                 | Rear wall mounting holes   |
|                                 | Quarter turn latch with slotted head insert                                    |
| Dimensions                      | Width: 760 mm  |
|                                 | Height: 760 mm   |
|                                 | Depth: 210 mm  |
|                                 | Width: 29.9 "  |
|                                 | Height: 29.9 "   |
|                                 | Depth: 8.27 ″  |
| Dimensions of mounting plate (W | 704 mm x 730 mm  |
| x H)                            | 27.7 ″ x 28.7 ″  |

© Rittal 2025 2

## Features

| NEMA 1        |
|---------------|
| NEMA 3R       |
| NEMA 4        |
| NEMA 12       |
| 2 mm          |
| 0.08 ~        |
| 1.5 mm        |
| 0.06 ″        |
| 2.5 mm        |
| 0.1 ″         |
| 1 pc(s).      |
| 83.333        |
| 87.743        |
| 8538100000    |
| 4028177532724 |
| 83112         |
|               |

## **Approvals**

| Approvals    | UL + C-UL (listed)        |
|--------------|---------------------------|
| Explanations | Declaration of conformity |

© Rittal 2025 3