Rittal - The System.

Faster – better – everywhere.





AX 1095.000 Basic enclosure AX, carbon steel

State: 11/2/2025 (Source: rittal.com/us-en)




AX 1095.000 - Basic enclosure AX, carbon steel

The AX wall-mounted enclosure with embossed enclosure cams in the roof, base and side replicates the familiar 25 mm system grid from the VX25 large enclosure. Thanks to this unique, patented system, AX wall-mounted control enclosures are prepared for all expansion and retrofit cases. System components and accessories can be installed and retrofitted easily, quickly and safely on rails without drilling.







Features

Model No.	AX 1095.000
Benefits	More interior finishing options thanks to integrated housing cams in the 25 mm system grid in combination with the rail for interior
	finishing and our wide range of system accessories
	Maintaining the protection class (UL approval) by mounting the rail
	for interior installation without drilling
	Additional mounting level and increased load capacity due to base
	configuration rail
	Easy planning and configuration with the Rittal configurator RiPanel
Material	Housing: Carbon steel
	Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035

© Rittal 2025 2

Features

Supply includes	Housing with door(s) Flange (gland) plate(s) in enclosure base Mounting panel Punched door strip Lock: 3 mm double-bit
Protection category IP to EN 60 529	IP 55
Type rating according to UL 50E	Type 1 Type 12
IK code	IK10
Dimensions	Width: 800 mm Height: 400 mm Depth: 300 mm Width: 31.5 " Height: 15.7 " Depth: 11.8 "
Material thickness - door	2 mm 0.08 ″
Material thickness - enclosure	1.5 mm 0.06 ″
Material thickness - mounting plate	2 mm 0.08 ″
Dimensions of mounting plate (W x H)	750 mm x 375 mm 29.5 ″ x 14.8 ″
Number of doors	2
No. of locks	2
Lock	Lock version: Cam Lock Insert: 3 mm double-bit
Gland plate	Size: 5 Qty.: 2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	24.577

© Rittal 2025 3

Features

Gross weight	24.889
Customs tariff number	94032080
EAN	4028177995246
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK

© Rittal 2025