Rittal – The System.

Faster – better – everywhere.



HD 1333.600

Compact enclosure HD, single-door

State: 11/15/2026 (Source: www.rittal.com/us-en)

HD 1333.600 - Compact enclosure HD, single-door

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs





Features

Model No.	HD 1333.600
Version	Hygienic Design Enclosures
Product changes	From June 2020, the compact enclosure HD, single-door, comes with the new compact enclosure AX mounting plate.
Material	Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel HD lock inserts: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Door with fitted seal Door hinged on the right, may be swapped to the left Mounting panel

© Rittal 2026

Features

Dimensions	Width: 940 mm Height, front: 1,575 mm Height rear: 1,745 mm Depth: 300 mm Width: 37 ″ Height, front: 62 ″ Height rear: 68.7 ″ Depth: 11.8 ″
Dimensions of mounting plate (W x H)	879 mm x 1,496 mm 34.6 ″ x 58.9 ″
Door opening angle	125°
No. of locks	2
IK code	IK08
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66 IP X9
Protection category NEMA	NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13
Type rating according to 508A	Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	223.997 lb
Gross weight	223.997 lb
Customs tariff number	9403200082

Features

ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	UL + C-UL (listed)