Rittal – The System.

Faster – better – everywhere.





KL 1505.510 KL Terminal Boxes

State: 11/9/2025 (Source: rittal.com/us-en)



KL 1505.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.



Features

Model No.	KL 1505.510
Material	Housing: Carbon steel
	Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover
	Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 500 mm
	Height: 200 mm
	Depth: 120 mm
	Width: 19.7 "
	Height: 7.87 "
	Depth: 4.72 "
Material thickness - cover	1.25 mm
	0.05 ″

© Rittal 2025

Features

Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.921
Gross weight	4.14
Customs tariff number	73269098
EAN	4028177251175
E-Number Sweden	E3404667
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity UK

© Rittal 2025 3