

**Rittal – The System.**

Faster – better – everywhere.



**KL 1510.510**

**KL Terminal Boxes**

State: 2/5/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



FRIEDHELM LOH GROUP

# KL 1510.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.



## Features

Model No.	KL 1510.510
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 600 mm Height: 300 mm Depth: 120 mm Width: 23.6 " Height: 11.8 " Depth: 4.72 "
Material thickness - cover	1.25 mm 0.05 "

# Features

---

Material thickness - enclosure	1.38 mm 0.05 "
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	6.513
Gross weight	6.856
Customs tariff number	73269098
EAN	4028177251229
E-Number Sweden	E3404672
ETIM 9	EC000261
ETIM 8	EC000261
ECCLASS 8.0	27180101

---

# Approvals

---

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity UK

---