Rittal – The System.

Faster – better – everywhere.





KL 1514.510 KL Terminal Boxes

State: 11/5/2025 (Source: rittal.com/us-en)



KL 1514.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.

Features

Model No.	KL 1514.510
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 150 mm Height: 150 mm Depth: 80 mm Width: 5.91 " Height: 5.91 " Depth: 3.15 "
Material thickness - cover	1.25 mm 0.05 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	1.012
Gross weight	1.212

© Rittal 2025

Features

Customs tariff number	73269098
EAN	4028177251267
E-Number Sweden	E3404676
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL
	Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity UK

© Rittal 2025 3