Rittal – The System.

Faster – better – everywhere.





KL 1517.510 KL Terminal Boxes

State: 11/12/2025 (Source: rittal.com/us-en)



KL 1517.510 - KL Terminal Boxes without gland plate

Spray-finished housing with sheet steel cover, without gland panel. Protection category IP 66.



Features

Model No.	KL 1517.510
Material	Housing: Carbon steel
	Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover
	Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 300 mm
	Height: 200 mm
	Depth: 80 mm
	Width: 11.8 "
	Height: 7.87 "
	Depth: 3.15 "
Material thickness - cover	1.25 mm
	0.05 ″

© Rittal 2025

Features

Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	2.2
Gross weight	2.4
Customs tariff number	73269098
EAN	4028177251298
E-Number Sweden	E3404679
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity UK

© Rittal 2025 3