

Rittal – The System.

Faster – better – everywhere.



BG 1558.510 BG Bus Housings

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1558.510 - BG Bus Housings

Wall-mounted enclosure with door of carbon steel, with polycarbonate viewing window.
Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Model No.	BG 1558.510
Material	Housing: Carbon steel Door: Carbon steel Viewing window: Polycarbonate, 4 mm ¹
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with door Viewing window in the door Flange plate in enclosure base
Protection category NEMA	NEMA 12
Protection category IP to EN 60529	IP 65
IK code	IK08
Dimensions	Width: 400 mm Height: 200 mm Depth: 125 mm Width: 15.7 " Height: 7.87 " Depth: 4.92 "
Material thickness - enclosure	1.25 mm 0.05 "
Material thickness - door	1.25 mm 0.05 "
Position door catch	bottom
Number of support rails	1

Features

Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.631 kg
Gross weight	3.8 kg
Customs tariff number	94032080
ECLASS 8.0	27180101
Product description	BG Bus enclosure, WHD: 400x200x125 mm, Sheet steel, with gland plate in the base and support rails, Door with viewing window, hinged at bottom

Approvals

Approvals	Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity