

Rittal – The System.

Faster – better – everywhere.



KL 1582.000

Plastic cable gland plates

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1582.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



Features

Model No.	KL 1582.000
Product description	With pre-punched PG holes for cable glands. Use with standard flange plate seal.
Material	ABS
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	6 2 2
Number x PG diameter	6 x 13.5 2 x 16 2 x 21
Dimensions	Width: 220 mm Depth: 90 mm Width: 8.66 " Depth: 3.54 "
Suitable for	Enclosure type: KL
Gland plate	Size: 2

Features

Operating temperature range	-40 °C...70 °C -40 °F...158 °F
Protection category IP to EN 60529	IP 55 if correctly installed
Packaging unit	5 pc(s).
Net weight	0.5 kg
Gross weight	0.581 kg
Customs tariff number	73269098
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	KL Plastic cable gland plate, with PG knock-outs, WD: 220x90 mm, size: 2, PG knockouts: 13.5