

Rittal – The System.

Faster – better – everywhere.



EL 2094.200

Captive nut

State: 6/10/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2094.200 - Captive nut

Captive nut, with M6 thread, with contact

Features

Model No.	EL 2094.200
Version	With contact
Product description	To fasten slide-in electronic equipment, 482.6 mm (19") installed equipment and blanking plates to profile rails. Used with profile plate thicknesses 0.8 – 2.5 mm. Either with or without contacting the installed equipment with the 482.6 mm (19") profile/housing.
Dimensions	Thread: M6
For material thicknesses	0.8 - 2.5 mm 0.03 - 0.1 "
Packaging unit	50 pc(s).
Net weight	0.2 kg
Gross weight	0.25 kg
Customs tariff number	73181692
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815
Product description	EL Captive nuts, M6, With contact, For metal thickness: 0,8-2,5 mm