

Rittal – The System.

Faster – better – everywhere.



EL 2246.605

Wall-mounted enclosures EL, 3-part

State: 4/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2246.605 - Wall-mounted enclosures EL, 3-part with mounting plate and profile rails, static installation

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, mounting plate is supplied loose. Protection category IP 55.

Features

| | |
|---------------------|--|
| Model No. | EL 2246.605 |
| Version | Wall-mounted housing IT with mounting plate and profile rails, static installation |
| Product description | Wall-mounted enclosure with hinged door provides optimum accessibility. |
| Material | Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| General color | RAL 7035 |
| Color | Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray) |
| Supply includes | Wall section with flange (gland) plate, top and bottom, and mounting plate (supplied loose). Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place Designer viewing door 1 enclosure key double bit no. 5 Mini-comfort handle for lock inserts Security lock 3524 E |
| Height units | 6 U |
| Dimensions | Width: 600 mm Height: 345 mm Depth: 373 mm Width: 23.6 " Height: 13.6 " Depth: 14.7 " |

Features

| | |
|---------------------------------------|--|
| Installation depth | 320 mm 12.6 " |
| Clearances | Clearance width: 502 mm Clearance height: 282 mm Clearance width: 19.8 " Clearance height: 11.1 " |
| Depth hinged part | 216 mm 8.5 " |
| Dimensions of mounting plate (W x H) | 485 mm x 299 mm 19.1 " x 11.8 " |
| Depth of wall section | 135 mm 5.31 " |
| IK code | IK08 |
| Load capacity of hinged part (static) | 300 N 67.443 lbf. |
| Base material | Carbon steel |
| Protection category IP to EN 60 529 | IP 55 |
| Packaging unit | 1 pc(s). |
| Net weight | 23.719 kg |
| Gross weight | 24.967 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002500 |
| ETIM 8 | EC002500 |
| ECLASS 8.0 | 27180208 |
| Product description | EL Wall-mounted enclosures, 3-part, 6 U, WHD: 600x345x373 mm, Protection category: IP 55, Designer glazed door |

Approvals

Approvals

Approvals

Lloyds Register of Shipping
UL + C-UL (listed)