

# Rittal – The System.

Faster – better – everywhere.



## EL 2253.605

## Wall-mounted enclosures EL, 3-part

State: 8/16/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# EL 2253.605 - Wall-mounted enclosures EL, 3-part with mounting plate and profile rails, static installation

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, mounting plate is supplied loose. Protection category IP 55.

## Features

Model No.	EL 2253.605
Version	Wall-mounted housing IT with mounting plate and profile rails, static installation
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section with flange (gland) plate, top and bottom, and mounting plate (supplied loose). Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place Designer viewing door 1 enclosure key double bit no. 5 Mini-comfort handle for lock inserts Security lock 3524 E
Height units	3 U
Dimensions	Width: 600 mm Height: 212 mm Depth: 473 mm Width: 23.6 " Height: 8.35 " Depth: 18.6 "

# Features

Installation depth	420 mm 16.5 "
Clearances	Clearance width: 502 mm Clearance height: 149 mm Clearance width: 19.8 " Clearance height: 5.87 "
Depth hinged part	316 mm 12.4 "
Dimensions of mounting plate (W x H)	485 mm x 165 mm 19.1 " x 6.5 "
Depth of wall section	135 mm 5.31 "
IK code	IK08
Load capacity of hinged part (static)	150 N 33.721 lbf.
Base material	Carbon steel
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	20.824
Gross weight	21.92
Customs tariff number	94032080
EAN	4028177324374
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180208

## Approvals

# Approvals

---

Approvals

Lloyds Register of Shipping  
UL + C-UL (listed)