Rittal - The System.

Faster – better – everywhere.





EL 2256.605 Wall-mounted enclosures EL, 3-part

State: 11/29/2025 (Source: rittal.com/us-en)



EL 2256.605 - Wall-mounted enclosures EL, 3-part with mounting plate and profile rails, static installation

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, mounting plate is supplied loose. Protection category IP 55.

Features

Model No.	EL 2256.605
Version	Wall-mounted housing IT
	with mounting plate and profile rails, static installation
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section with flange (gland) plate, top and bottom, and
	mounting plate (supplied loose).
	Hinged part with 25 mm pitch pattern in the front and rear frame
	two 19" profile angles at the front, fixed in place
	Designer viewing door
	1 enclosure key double bit no. 5
	Mini-comfort handle for lock inserts
	Security lock 3524 E
Height units	6 U
Dimensions	Width: 600 mm
	Height: 345 mm
	Depth: 473 mm
	Width: 23.6 "
	Height: 13.6 "
	Depth: 18.6 "

© Rittal 2025 2

Features

Installation depth	420 mm
	16.5 ″
Clearances	Clearance width: 502 mm
	Clearance height: 282 mm
	Clearance width: 19.8 "
	Clearance height: 11.1 "
Depth hinged part	316 mm
	12.4 ″
Dimensions of mounting plate (W	485 mm x 299 mm
x H)	19.1 ″ x 11.8 ″
Depth of wall section	135 mm
	5.31 ″
IK code	IK08
Load capacity of hinged part	300 N
(static)	67.443 lbf.
Base material	Carbon steel
Protection category IP to EN 60	IP 55
529	
Packaging unit	1 pc(s).
Net weight	25.969
Gross weight	27.336
Customs tariff number	94032080
EAN	4028177324381
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180208

Approvals

© Rittal 2025 3

Approvals

Approvals

Lloyds Register of Shipping UL + C-UL (listed)

© Rittal 2025 4