

# Rittal – The System.

Faster – better – everywhere.



## AX 2260.950

## AX wall-mounted housing, 3-part

State: 4/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2260.950 - AX wall-mounted housing, 3-part

The delivery concept of the three-part AX wall-mounted enclosure reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.



## Features

|                 |  |
|-----------------|--|
| Model No.       | AX 2260.950  |
| Version         | Wall-mounted housing IT  |
| Material        | Wall and hinged part: Carbon steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm   |
| Surface finish  | Powder-coated  |
| Color           | Wall and hinged part: RAL 7035<br>Viewing door: RAL 7035/7015 (slate gray)   |
| Supply includes | Wall section: Flange (gland) plate, solid, top and bottom<br>Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place<br>Designer viewing door<br>Center part lock: 3 mm double bit<br>Lock design – glazed door: Security lock 3524 E<br>Mini-comfort handle |
| Height units    | 9 U  |

# Features

|                                       |  |
|---------------------------------------|--|
| Dimensions                            | Width: 600 mm<br>Height: 478 mm<br>Depth: 573 mm<br>Width: 23.6 "<br>Height: 18.8 "<br>Depth: 22.6 "                 |
| Installation depth                    | 520 mm<br>20.5 "   |
| Clearances                            | Clearance width: 502 mm<br>Clearance height: 417 mm<br>Clearance width: 19.8 "<br>Clearance height: 16.4 "           |
| Depth hinged part                     | 416 mm<br>16.4 "   |
| Depth of wall section                 | 135 mm<br>5.31 "   |
| No. of locks                          | 1  |
| Load capacity of hinged part (static) | 450 N  |
| Load capacity wall section (static)   | 150 N  |
| Base material                         | Carbon steel   |
| Lock                                  | Lock version: Mini-comfort handle<br>Lock Insert: Security lock insert no. 3524 E                                    |
| Protection category IP to EN 60529    | IP 54 in conjunction with solid gland plate top and bottom   |
| Packaging unit                        | 1 pc(s).   |
| Net weight                            | 30 kg  |
| Gross weight                          | 32.6 kg  |
| Information regarding the PCF class   | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number                 | 94032080   |
| ETIM 9                                | EC002500   |

# Features

---

|                     |   |
|---------------------|---|
| ETIM 8              | EC002500  |
| ECLASS 8.0          | 27180101  |
| Product description | AX wall-mounted housing AX, 3-part, WHD: 600x478x573 mm, 9 HE, wall section: closed flange plate top and bottom, with mini comfort handle |

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|