
Rittal – The System.

Faster – better – everywhere.



SZ 2311.225

Spacers

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2311.225 - Spacers

Universal assembly component for all situations where spacing to the mounting level is required.

Features

Model No.	SZ 2311.225
Product description	Utilized to mount components at an offset from mounting panel surface.
Technical specifications	With self-tapping thread for Ø 4.5 mm holes
Material	Hexagonal steel (SW8)
Surface finish	Zinc-plated
Length	25 mm 0.98 ″
Mounting tip	On the rear, 5.5 x 13 carbon steel screws can be used, for example to fix top hat/support profile rails, contact hazard protection covers, main switch trim panels, and cable clamp rails, etc.
Packaging unit	12 pc(s).
Net weight	0.108 kg
Gross weight	0.118 kg
PCF/VE (cradle-to-gate)	0.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73181535
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234
Product description	SZ Spacer, L: 25 mm

© Rittal 2026