

Rittal – The System.

Faster – better – everywhere.



SR 2323.235

Pivoting frame, large, with trim panel

State: 6/19/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2323.235 - Pivoting frame, large, with trim panel for TS, VX SE, 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel to mount 482.6 mm (19") rack-mounted equipment.



Features

Model No.	SR 2323.235
Version	19" level side
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Frame: Zinc-plated Panel: Spray-finished
Color	RAL 7035
Supply includes	Locking rod system with double-bit lock insert Material for attaching
Installation options	In TS/SE with opening angle of 130° or 180°, depending on the selected installation kit

Features

Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options In the case of TS and SE two-door enclosures with heights of 1800 mm or 2200 mm, the next smallest pivoting frame must be fitted to prevent a collision with the lock
Suitable for	Enclosure type: TS VX SE Width: = 800 mm Height: ≥ 1,200 mm Enclosure type: TS VX SE Width: = 31.5 " Height: ≥ 47.2 "
Height units	22 U
Suitable for enclosure type	TS VX SE
Packaging unit	1 pc(s).
Net weight	12.888 kg
Gross weight	13.566 kg
Customs tariff number	94039910
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	SR pivoting frame, large, with trim panel, for TS, VX SE, for W: 800 mm, 22 U, side installation