

# Rittal – The System.

Faster – better – everywhere.



## SR 2331.700

# Pivoting Frame, large, without trim panel

State: 5/22/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SR 2331.700 - Pivoting Frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, to mount 482.6 mm (19") equipment.



## Features

Model No.	SR 2331.700
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options
Suitable for	Enclosure type: TS Width: = 600 mm = 1,200 mm Height: ≥ 1,600 mm Enclosure type: TS Width: = 23.6 " = 47.2 " Height: ≥ 63 "
Height units	31 U

# Features

Suitable for enclosure type	TS
Packaging unit	1 pc(s).
Net weight	10.425 kg
Gross weight	10.974 kg
Customs tariff number	94039910
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	SR pivoting frame, large, without cover, for TS, VX SE, for W: 600/1200 mm, 31 U