### Rittal - The System.

Faster – better – everywhere.





SR 2331.700

# Pivoting Frame, large, without trim panel


State: 11/25/2025 (Source: rittal.com/us-en)



## SR 2331.700 - Pivoting Frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, to mount 482.6 mm (19") equipment.





#### **Features**

Model No.	SR 2331.700
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options
Suitable for	Enclosure type: TS  Width: = 600 mm  = 1,200 mm  Height: $\geq$ 1,600 mm  Enclosure type: TS  Width: = 23.6 "  = 47.2 "  Height: $\geq$ 63 "
Height units	31 U

© Rittal 2025

### **Features**

Suitable for enclosure type	TS
Packaging unit	1 pc(s).
Net weight	10.425
Gross weight	10.974
Customs tariff number	94039910
EAN	4028177021426
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3