


Rittal – The System.

Faster – better – everywhere.



SR 2336.700

Pivoting Frame, large, without trim panel

State: 11/25/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2336.700 - Pivoting Frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, to mount 482.6 mm (19") equipment.



Features

Model No.	SR 2336.700
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options
Suitable for	Enclosure type: TS Width: = 600 mm = 1,200 mm Height: ≥ 1,800 mm Enclosure type: TS Width: = 23.6 " = 47.2 " Height: ≥ 70.9 "
Height units	36 U

Features

Suitable for enclosure type	TS
Packaging unit	1 pc(s).
Net weight	11.939
Gross weight	12.567
Customs tariff number	94039910
EAN	4028177021556
ECLASS 8.0	27189261