Rittal – The System.

Faster – better – everywhere.





SR 2337.235

Pivoting frame, large, with trim panel

State: 11/10/2025 (Source: rittal.com/us-en)



SR 2337.235 - Pivoting frame, large, with trim panel for TS, VX SE, 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel to mount 482.6 mm (19") rack-mounted equipment.





Features

CD 2227 225
SR 2337.235
19" level side
To mount 482.6 mm (19") equipment.
Carbon steel
Frame: Zinc-plated Panel: Spray-finished
RAL 7035
Locking rod system with double-bit lock insert Material for attaching
In TS/SE with opening angle of 130° or 180°, depending on the selected installation kit

© Rittal 2025 2

Features

Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options In the case of TS and SE two-door enclosures with heights of 1800 mm or 2200 mm, the next smallest pivoting frame must be fitted to prevent a collision with the lock
Suitable for	Enclosure type: TS VX SE Width: = 800 mm Height: ≥ 1,800 mm Enclosure type: TS VX SE Width: = 31.5 " Height: ≥ 70.9 "
Height units	36 U
Suitable for enclosure type	TS VX SE
Packaging unit	1 pc(s).
Net weight	18.147
Gross weight	19.402
Customs tariff number	94039910
EAN	4028177165168
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3