


# Rittal – The System.

Faster – better – everywhere.



## SR 2340.700

## Pivoting Frame, large, without trim panel

State: 7/13/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SR 2340.700 - Pivoting Frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, to mount 482.6 mm (19") equipment.



## Features

Model No.	SR 2340.700
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Cam with double-bit lock insert Parts for attaching to the installation kit
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options
Suitable for	Enclosure type: TS Width: = 600 mm = 1,200 mm Height: ≥ 2,000 mm Enclosure type: TS Width: = 23.6 " = 47.2 " Height: ≥ 78.7 "
Height units	40 U

# Features

Suitable for enclosure type	TS
Packaging unit	1 pc(s).
Net weight	12.271
Gross weight	12.917
Customs tariff number	94039910
EAN	4028177021679
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261