


Rittal – The System.

Faster – better – everywhere.



AX 2361.010

Canopy

State: 6/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2361.010 - Canopy for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.



Features

Model No.	AX 2361.010
Product description	The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 240
Supply includes	Assembly components
Installation options	Can be screw-fastened for dynamic loads
Dimensions	Height: 37 mm Height: 1.46 "
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12

Features

Suitable for	Enclosure type: AX Width: = 300 mm Depth: = 210 mm Enclosure type: AX Width: = 11.8 " Depth: = 8.27 "
Packaging unit	1 pc(s).
Net weight	1.3 kg
Gross weight	1.458 kg
Customs tariff number	94039910
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405
Product description	AX Protective roof, for WD: 300x210 mm, stainless steel

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------