Rittal – The System.

Faster – better – everywhere.



AX 2364.010

Canopy

State: 11/14/2026 (Source: www.rittal.com/us-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES


FRIEDHELM LOH GROUP

AX 2364.010 - Canopy for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.







Features

Model No.	AX 2364.010
Product description	The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 240
Supply includes	Assembly components
Installation options	Can be screw-fastened for dynamic loads
Dimensions	Height: 43 mm Height: 1.69 ″
Type rating according to 508A	Type 1 Type 3R Type 4 Type 4X Type 12

© Rittal 2026

Features

Suitable for	Enclosure type: AX Width: = 800 mm Depth: = 400 mm Enclosure type: AX Width: = 31.5 ″ Depth: = 15.7 ″
Packaging unit	1 pc(s).
Net weight	4.9 kg
Gross weight	5.161 kg
Customs tariff number	94039910
ECLASS 8.0	27182405
Product description	AX canopy for W x D: 800 x 400 mm, stainless steel

Approvals

Approvals	UL + C-UL - FTTA