


Rittal – The System.

Faster – better – everywhere.



SG 2369.020

Steady light component

State: 1/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2369.020 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2369.020
Version	Steady light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Yellow
Diameter	70 mm 2.76 "
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Note on Model No.:	Incandescent lamps not included with the supply.
Dimensions	Height: 56 mm Height: 2.2 "
Protection category IP to EN 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	12 V - 240 V (AC/DC)
Packaging unit	1 pc(s).

Features

Net weight	0.07
Gross weight	0.094
Customs tariff number	85311095
EAN	4028177219946
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------