

# Rittal – The System.

Faster – better – everywhere.



## SG 2369.030

## Steady light component

State: 1/30/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2369.030 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

## Features

|                                                 |                                                                                                                                                                                 |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                                       | SG 2369.030                                                                                                                                                                     |
| Version                                         | Steady light component                                                                                                                                                          |
| Product description                             | With 360° signal transmission thanks to optimized prism system.<br>Number of potential stages = 5 components, with identical voltage.                                           |
| Benefits                                        | Easy mounting and contact via bayonet fastener.<br>Configuration of up to five components with the same voltage.<br>Components are available in a range of colors and voltages. |
| Function principle                              | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.                                                            |
| Material                                        | Housing of polyamide<br>Cap: Transparent polycarbonate                                                                                                                          |
| Color                                           | Clear                                                                                                                                                                           |
| Diameter                                        | 70 mm<br>2.76 "                                                                                                                                                                 |
| Rated impulse withstand voltage, phase to phase | 2500 V AC                                                                                                                                                                       |
| Rated insulation voltage                        | 250 V AC                                                                                                                                                                        |
| Note on Model No.:                              | Incandescent lamps not included with the supply.                                                                                                                                |
| Dimensions                                      | Height: 56 mm<br>Height: 2.2 "                                                                                                                                                  |
| Protection category IP to EN 60 529             | IP 54 if a cover or acoustic component is fitted at the top                                                                                                                     |
| Rated operating voltage                         | 12 V - 240 V (AC/DC)                                                                                                                                                            |
| Packaging unit                                  | 1 pc(s).                                                                                                                                                                        |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 0.07          |
| Gross weight          | 0.08          |
| Customs tariff number | 85311095      |
| EAN                   | 4028177219953 |
| ECLASS 8.0            | 27371220      |

# Approvals

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|