


Rittal – The System.

Faster – better – everywhere.



SG 2370.170

LED steady light component

State: 11/22/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2370.170 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, number of potential stages = 5 components, with identical voltage.

Features

| | |
|---|---|
| Model No. | SG 2370.170 |
| Version | LED steady light component |
| Product description | With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage. |
| Benefits | Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. |
| Function principle | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel. |
| Material | Housing of polyamide Cap: Transparent polycarbonate |
| Color | Yellow |
| Diameter | 70 mm 2.76 " |
| Rated impulse withstand voltage, phase to phase | 2500 V AC |
| Rated insulation voltage | 250 V AC |
| Dimensions | Height: 56 mm Height: 2.2 " |
| Protection category IP to EN 60529 | IP 54 if a cover or acoustic component is fitted at the top |
| Rated operating voltage | 230 V |
| Packaging unit | 1 pc(s). |
| Net weight | 0.07 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 0.083 |
| Customs tariff number | 94054990 |
| EAN | 4028177656437 |
| ECLASS 8.0 | 27371220 |

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|