


Rittal – The System.

Faster – better – everywhere.



SZ 2370.510

LED flashing light component

State: 1/31/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2370.510 - LED flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

Features

Model No.	SZ 2370.510
Version	LED flashing light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Green
Diameter	70 mm 2.76 "
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Dimensions	Height: 56 mm Height: 2.2 "
Protection category IP to EN 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)

Features

Packaging unit 1 pc(s).

Net weight 0.07

Gross weight 0.083

Customs tariff number 94054990

EAN 4028177656468

ECLASS 8.0 27371220

Approvals

Approvals UL + C-UL (listed)
UR