


Rittal – The System.

Faster – better – everywhere.



SG 2370.511

LED flashing light component

State: 9/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2370.511 - LED flashing light component for signal pillar, modular

With 360° signal transmission due to optimized prism system.

Features

| | |
|-------------------------------------|---|
| Model No. | SG 2370.511 |
| Version | LED flashing light component |
| Benefits | Easy mounting and contact via bayonet fastener. With 360° signal transmission thanks to optimized prism system Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. |
| Function principle | A modular layout is possible with connection, optical and acoustic components and a label panel |
| Material | Housing of polyamide Cap: Transparent polycarbonate |
| Color | Green |
| Protection category IP to EN 60 529 | IP 65, when cover or acoustic component is mounted on top |
| Rated operating voltage | 24 V (AC/DC) |
| Packaging unit | 1 pc(s). |
| Net weight | 0.07 |
| Gross weight | 0.073 |
| Customs tariff number | 85311095 |
| EAN | 4028177953635 |
| ETIM 9 | EC000232 |
| ETIM 8 | EC000232 |
| ECLASS 8.0 | 27371220 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |