

# Rittal – The System.

Faster – better – everywhere.



## SG 2372.130

## Signal pillar, LED compact

State: 5/5/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2372.130 - Signal pillar, LED compact

Extremely long service life LEDs, minimal assembly work and low storage costs.

## Features

Model No.	SG 2372.130
Version	1-stage, red
Product description	Angle of reflected beam: 3 x 120°, as delivered: Steady light. Flashing function PLC controllable
Benefits	Complete, ready-to-connect solution Minimal build height Long service life of the LEDs Minimal assembly work and warehousing costs
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm Min. cable diameter: 0.12 " Max. cable diameter: 0.26 "
Diameter	72 mm 2.83 "
Type of connection (electrical)	Screw clamps
Light (bulb)	LEDs
Rated insulation voltage	< 60 V DC
Dimensions	Height: 107 mm Height: 4.21 "
Operating temperature range	-20 °C...70 °C -4 °F...158 °F
Protection category IP to EN 60 529	IP 65
Rated operating voltage	24 V 24 V (DC)
Packaging unit	1 pc(s).
Net weight	0.219

# Features

Gross weight	0.233
Customs tariff number	85311095
EAN	4028177490130
ECLASS 8.0	27371230

# Approvals

Approvals	UR
Explanations	Declaration of conformity Declaration of conformity UK