

**Rittal – The System.**

Faster – better – everywhere.



**SG 2372.130**

**Signal pillar, LED compact**

State: 1/30/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))



FRIEDHELM LOH GROUP

# SG 2372.130 - Signal pillar, LED compact

Extremely long service life LEDs, minimal assembly work and low storage costs.

## Features

Model No.	SG 2372.130
Version	1-stage, red
Product description	Angle of reflected beam: 3 x 120°, as delivered: Steady light. Flashing function PLC controllable
Benefits	Complete, ready-to-connect solution Minimal build height Long service life of the LEDs Minimal assembly work and warehousing costs
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm Min. cable diameter: 0.12 " " Max. cable diameter: 0.26 "
Diameter	72 mm 2.83 "
Type of connection (electrical)	Screw clamps
Light (bulb)	LEDs
Rated insulation voltage	< 60 V DC
Dimensions	Height: 107 mm Height: 4.21 "
Operating temperature range	-20 °C...70 °C -4 °F...158 °F
Protection category IP to EN 60 529	IP 65
Rated operating voltage	24 V 24 V (DC)
Packaging unit	1 pc(s).
Net weight	0.219

## Features

---

Gross weight	0.233
Customs tariff number	85311095
EAN	4028177490130
ECLASS 8.0	27371230

---

## Approvals

---

Approvals	UR
Explanations	<a href="#">Declaration of conformity</a> <a href="#">Declaration of conformity UK</a>

---