

# Rittal – The System.

Faster – better – everywhere.



## SG 2376.010

## Acoustic component

State: 4/12/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2376.010 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

## Features

Model No.	SG 2376.010
Version	Volume and 8 tones may be set, 100 dB, max. 25 mA
Product description	To indicate warnings or malfunctions.
Benefits	Easy mounting and contact via bayonet fastener.
Applications	Mounting only on the upper end of the optical components or directly on the connection component
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide
Color	Black
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Rated operating voltage	24 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.1 kg
Gross weight	0.115 kg
Customs tariff number	85311095
ECLASS 8.0	27371237
Product description	SG Acoustic component, for signal pillar, modular, 24 V AC/DC, 100 dB, max. 25 mA

# Approvals

---

Approvals

UR