

Rittal – The System.

Faster – better – everywhere.



SG 2376.011

Acoustic component

State: 12/22/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2376.011 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

Features

Model No.	SG 2376.011
Version	Volume and 8 tones available, 102 dB
Product description	To indicate warnings or malfunctions.
Material	Housing of polyamide
Color	Black
Mounting tip	Mounting only on the upper end of the optical components or directly on the connection component
Protection category IP to EN 60 529	IP 65
Rated operating voltage	24 V
Packaging unit	1 pc(s).
Net weight	0.087
Gross weight	0.088
Customs tariff number	85311095
EAN	4028177953789
ETIM 9	EC001261
ETIM 8	EC001261
ECLASS 8.0	27371237

Approvals

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity