Rittal - The System.

Faster – better – everywhere.





AE 2383.250 Rail for Interior Installation

State: 10/23/2025 (Source: rittal.com/us-en)



AE 2383.250 - Rail for Interior Installation for AE/WM

Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



Features

Model No.	AE 2383.250
Product description	Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable, with 2 rows of system punchings, provides additional mounting space for: TS system chassis, enclosure lights, door-operated switch, door stay, cable conduit holder
Material	Carbon steel
Surface finish	Zinc-plated
Note	Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000
Suitable for	Enclosure type: AE Depth: = 250 mm Enclosure type: AE Depth: = 9.84 ~
Packaging unit	4 pc(s).
Net weight	0.72
Gross weight	0.8
Customs tariff number	73269098

© Rittal 2025

2

Features

EAN	4028177687424
E-Number Sweden	E3404333
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3