Rittal – The System.

Faster – better – everywhere.



# AE 2383.300

# Rail for Interior Installation

State: 11/4/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AE 2383.300 - Rail for Interior Installation for AE/WM

Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



## Features

| | |
|---|---|
| Model No. | AE 2383.300 |
| Product description | Mounted in the housing, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable, with 2 rows of system punchings, provides additional mounting space for: TS system chassis, enclosure lights, door-operated switch, door stay, cable conduit holder |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Note | Other mounting options: Mounting plates, locatable, TS 8612.400<br>Mounting plates, screw-fastening, large, TS 8612.410<br>Mounting plates, screw-fastening, small, PS 4532.000<br>Mounting bracket, PS 4597.000 |
| Suitable for | Enclosure type: AE<br>Depth: = 300 mm<br>Enclosure type: AE<br>Depth: = 11.8 ″ |
| Packaging unit | 4 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 0.92 kg |
| Customs tariff number | 73269098 |

# Features

| | |
|---|---|
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | AE Rail for interior installation, for AE, for D: 300 mm |

© Rittal 2026