Rittal – The System.

Faster – better – everywhere.



SZ 2412.210
Grounding Braid

State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2412.210 - Grounding Braid

Tin-plated copper, in various lengths and cross-sections with press-fit contact rings, to counteract the proximity effect at high frequencies, while offering flexible connection options.





Features

Model No.	SZ 2412.210
Product description	Tin-plated copper, in various lengths and cross-sections with press-fit contact rings. Grounding braids counteract the proximity effect at high frequencies, while offering flexible connection options.
Cross-section	10 mm²
Connection	M6 – M6
Note	Please refer to the installation instructions or equipment grounding conductor brochure of the respective enclosure or housing system.
Dimensions	Length: 200 mm Length: 7.87 ˝
Packaging unit	10 pc(s).
Net weight	0.21 kg
Gross weight	0.26 kg
Customs tariff number	74198010
ETIM 9	EC000839
ETIM 8	EC000839
ECLASS 8.0	27062302
Product description	SZ Earthing strap, size: M6, for diameter 10 mm²

Approvals

Approvals	UL + C-UL (listed)