

# Rittal – The System.

Faster – better – everywhere.



## SZ 2412.225 Grounding Braid

State: 9/7/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2412.225 - Grounding Braid

Tin-plated copper, in various lengths and cross-sections with press-fit contact rings, to counteract the proximity effect at high frequencies, while offering flexible connection options.



## Features

Model No.	SZ 2412.225
Product description	Tin-plated copper, in various lengths and cross-sections with press-fit contact rings. Grounding braids counteract the proximity effect at high frequencies, while offering flexible connection options.
Cross-section	25 mm <sup>2</sup>
Connection	M8 – M8
Note	Please refer to the installation instructions or equipment grounding conductor brochure of the respective enclosure or housing system.
Dimensions	Length: 200 mm Length: 7.87 "
Packaging unit	10 pc(s).
Net weight	0.45
Gross weight	0.562
Customs tariff number	74198010
EAN	4028177022577
ETIM 9	EC000839
ETIM 8	EC000839
ECLASS 8.0	27062302

# Approvals

---

Approvals

UL + C-UL (listed)