
Rittal - The System.

Faster - better - everywhere.





SZ 2412.316 **Grounding Braid**

State: 12/7/2025 (Source: rittal.com/us-en)



SZ 2412.316 - Grounding Braid

Tin-plated copper, in various lengths and cross-sections with press-fit contact rings, to counteract the proximity effect at high frequencies, while offering flexible connection options.



Features

Model No.	SZ 2412.316
Product description	Tin-plated copper, in various lengths and cross-sections with press- fit contact rings. Grounding braids counteract the proximity effect at high frequencies, while offering flexible connection options.
Cross-section	16 mm²
Connection	M8 – M8
Note	Please refer to the installation instructions or equipment grounding conductor brochure of the respective enclosure or housing system.
Dimensions	Length: 300 mm Length: 11.8 ″
Packaging unit	10 pc(s).
Net weight	0.42
Gross weight	0.52
Customs tariff number	74198010
EAN	4028177022591
ETIM 9	EC000839
ETIM 8	EC000839
ECLASS 8.0	27062302

© Rittal 2025

Approvals

Approvals

UL + C-UL (listed)

© Rittal 2025 3