


# Rittal – The System.

Faster – better – everywhere.



## SZ 2422.000 Spacer

State: 12/19/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2422.000 - Spacer for roof plate

For raising the roof for ventilation purposes, available in three different heights. Not suitable for crane transport.



## Features

Model No.	SZ 2422.000
Product description	For raising the roof for ventilation purposes, available in three different heights.
Material	Hexagon steel section
Surface finish	Zinc-plated
Supply includes	Assembly components
Mounting tip	Not suitable for crane transportation
Dimensions	Height: 10 mm Height: 0.39 "
Dimensions	Thread: M12
Suitable for	Enclosure type: VX TS
Packaging unit	4 pc(s).
Net weight	0.12
Gross weight	0.161
PCF/VE (cradle-to-gate)	0.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

# Features

Customs tariff number	73269098
EAN	4028177022775
E-Number Sweden	E7239751
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234