

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2433.010**

**Wall mounting bracket**

State: 4/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2433.010 - Wall mounting bracket for stainless steel AX

For mounting AX and KX stainless steel enclosures.

## Features

|                                 |  |
|---------------------------------|--|
| Model No.                       | SZ 2433.010  |
| Product description             | For mounting AX and KX stainless steel housings.   |
| Benefits                        | Simple location of the wall bracket on a pre-configured screw in the wall<br>The wall mounting can be optimally adapted to the local conditions via various mounting positions<br>If required, the holder can be fitted with a stylish cover cap |
| Material                        | Stainless steel 1.4301 (AISI 304)  |
| Supply includes                 | Wall mounting bracket<br>Cover Caps<br>Assembly components   |
| Wall distance                   | 20 mm<br>0.79 "  |
| Note                            | For hygiene reasons, and to retain the protection category, the stainless steel enclosures do not have any drilled holes for the wall-mounting brackets.   |
| Suitable for                    | Enclosure type: AX stainless steel<br>KX stainless steel   |
| Type rating according to UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12  |
| Packaging unit                  | 4 pc(s).   |
| Net weight                      | 0.4 kg   |
| Gross weight                    | 0.42 kg  |

# Features

---

|                       |   |
|-----------------------|---|
| Customs tariff number | 83025000  |
| ETIM 9                | EC002625  |
| ETIM 8                | EC002625  |
| ECLASS 8.0            | 27189234  |
| Product description   | SZ Wall mounting bracket, for AX and KX, stainless steel 1.4301, wall distance: 20 mm |

---

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|