
Rittal - The System.

Faster - better - everywhere.





AX 2475.010 Canopy


State: 11/4/2025 (Source: rittal.com/us-en)



AX 2475.010 - Canopy for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.







Features

| Model No. | AX 2475.010 |
|---------------------------------|---|
| Product description | The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 240 |
| Supply includes | Assembly components |
| Installation options | Can be screw-fastened for dynamic loads |
| Dimensions | Height: 43 mm Height: 1.69 ″ |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |

© Rittal 2025 2

Features

| Suitable for | Enclosure type: AX Width: = 800 mm Depth: = 300 mm |
|-----------------------|--|
| | Enclosure type: AX |
| | Width: = 31.5 " |
| | Depth: = 11.8 " |
| Packaging unit | 1 pc(s). |
| Net weight | 3.56 |
| Gross weight | 4.02 |
| Customs tariff number | 94039910 |
| EAN | 4028177938250 |
| E-Number Sweden | E3465268 |
| ETIM 9 | EC000744 |
| ETIM 8 | EC000744 |
| ECLASS 8.0 | 27182405 |

Approvals

Approvals UL + C-UL - FTTA