


Rittal – The System.

Faster – better – everywhere.



AX 2476.010

Canopy

State: 2/1/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2476.010 - Canopy for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.



Features

Model No.	AX 2476.010
Product description	The sloping protective roof reliably protects the enclosure from standing moisture and other dirt from above.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 240
Supply includes	Assembly components
Installation options	Can be screw-fastened for dynamic loads
Dimensions	Height: 47 mm Height: 1.85 "
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12

Features

Suitable for	Enclosure type: AX Width: = 600 mm Depth: = 350 mm
	Enclosure type: AX Width: = 23.6 "
	Depth: = 13.8 "
Packaging unit	1 pc(s).
Net weight	3.48
Gross weight	3.68
Customs tariff number	94039910
EAN	4028177938267
E-Number Sweden	E3465266 E3465269
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------