## Rittal – The System.

Faster - better - everywhere.





# SZ 2500.104 LED system light

State: 12/13/2025 (Source: rittal.com/us-en)



## SZ 2500.104 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.





#### **Features**

Model No.	SZ 2500.104
Version	without socket
Benefits	Optimum illumination of the entire enclosure
	Option of clip-on, screw or magnetic attachment
	A configuration to suit every application
Version	without socket
Material	Light body: Extruded aluminum
	Light cover: polycarbonate
	Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	5 W
Connection options	Power Supply, 2-pole
	Through-wiring, 2-pole
	Door-operated switch
Protection category	II (total insulation)

© Rittal 2025

### Features

Light – installation type	Screw fastening Clip fastening Magnetic fastener (accessories)
Installation options	The internal mounting rail AX and the mounting bracket are required when installing in compact enclosures
Luminous flux	400 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 262 mm  Height: 55 mm  Depth: 23 mm  Width: 10.3 "  Height: 2.17 "  Depth: 0.91 "
Operating temperature range	-20 °C55 °C -4 °F131 °F
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz
Protection category IP to IEC 60 529	IP 20
Packaging unit	1 pc(s).
Net weight	0.28
Gross weight	0.287
Customs tariff number	94054990
EAN	4028177920538
E-Number Sweden	E3465307
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

© Rittal 2025 3

## Approvals

Approvals	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025