Rittal – The System.

Faster – better – everywhere.




SZ 2500.470
Door-Operated Switch

State: 11/10/2026 (Source: www.rittal.com/us-en)

SZ 2500.470 - Door-Operated Switch for LED System Light

For simple, time-saving connection of the LED system light.



Features

Model No.	SZ 2500.470
Version	With connection cable
Product description	For simple, time-saving connection of the LED system light.
Color	Black
Supply includes	Assembly components
Cross-section	0.75 mm²
Length	800 mm 31.5 ″
AWG	AWG 18
Standards	Mains connection cables: CYJV2 Door-operated switch: NKCR
Dimensions	Width: 31 mm Height: 78 mm Depth: 30 mm Length: 800 mm Width: 1.22 ″ Height: 3.07 ″ Depth: 1.18 ″ Length: 31.5 ″
Electrical connection	2.5 A
Rated operating voltage	230 V (AC) 24 V (DC)

Features

Packaging unit	1 pc(s).
Net weight	0.1 kg
Gross weight	0.11 kg
Customs tariff number	85365019
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266
Product description	SZ Door-operated switch, with connection wire, L: 800 mm, black, UL

Approvals

Approvals	CQC CQC-CCC UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK