Rittal – The System.

Faster – better – everywhere.




SZ 2500.710
Socket box


State: 10/31/2026 (Source: www.rittal.com/us-en)

SZ 2500.710 - Socket box for LED System Light

In combination with the LED system light, the socket box creates a flexible modular system for international use.







Features

Model No.	SZ 2500.710
Product description	In combination with the LED system light, the socket box creates a flexible modular system for international use.
Benefits	Similar connection accessories as for LED system lights Cascadable with LED system light Flexible mounting possible throughout the enclosure and on the tubular door frame Ergonomic positioning of the socket box on surfaces No additional wiring required, due to simple connection technology and integration of the LED system light into the circuit
Material	Plastic
Color	RAL 7016
Supply includes	Assembly components
Connection options	Power Supply, 3-pole Through-wiring, 3-pole
Note	Through-wiring or a 3-pole infeed is necessary depending on the application

© Rittal 2026

Features

Dimensions	Width: 163 mm Height: 68 mm Depth: 43.5 mm Width: 6.42 ″ Height: 2.68 ″ Depth: 1.71 ″
Operating temperature range	-20 °C...55 °C -4 °F...131 °F
Outlets	D, ground pin (type F, CEE 7/3)
Rated operating voltage	195 V - 250 V, 50 Hz/60 Hz
Packaging unit	1 pc(s).
Net weight	0.26 kg
Gross weight	0.28 kg
PCF/VE (cradle-to-gate)	1.6
Customs tariff number	85366990
ETIM 9	EC000330
ETIM 8	EC000330
ECLASS 8.0	27142604
Product description	Socket box for LED system light, with socket for Germany, with earthing-pin (type F, CEE 7/3)

Approvals

Explanations	Declaration of conformity PCF-declaration