

Rittal – The System.

Faster – better – everywhere.



SZ 2561.500

Plastic cable gland plates

State: 12/9/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

Features

Model No.	SZ 2561.500
Product description	Just pierce the plastic with a sharp point and pull the cable through.
Material	Plastic to UL 94-V0 Halogen-free
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 330 mm Depth: 90 mm Width: 13 ~ Depth: 3.54 ~
Suitable for	Enclosure type: AE
Gland plate	Size: 3
Protection category IP to EN 60529	IP 65
Quantity of cable entries and Ø (mm) min.-max.	17 x 6-11 27 x 10-15 2 x 15-21 4 x 16-25 2 x 19-34
Packaging unit	1 pc(s).
Net weight	0.365
Gross weight	0.37
Customs tariff number	39269097
EAN	4028177325593

Features

E-Number Sweden	E3404727
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421