



SZ 2562.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

Features

Model No.	SZ 2562.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	2 x M16 5 x M20 13 x M25 2 x M32 2 x M40
Dimensions	Width: 339 mm Depth: 149 mm Width: 13.3 " Depth: 5.87 "
Suitable for	Enclosure type: AE
Gland plate	Size: 4
Protection category IP to EN 60529	IP66 when mounting in the usual position at the bottom
Packaging unit	1 pc(s).
Net weight	0.5 kg
Gross weight	0.62 kg
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211

Features

ECLASS 8.0

27142421

Product description

SZ Metal gland plate, with metric knock-outs, WD: 339x149 mm,
size: 4