

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2562.100

## Metal gland plate

State: 4/28/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | SZ 2562.100   |
| Product description                | Simply knock out the holes for the cable glands with a screwdriver.             |
| Material                           | Carbon steel  |
| Color                              | RAL 7035  |
| Note                               | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts            | 2 x M16<br>5 x M20<br>13 x M25<br>2 x M32<br>2 x M40                            |
| Dimensions                         | Width: 339 mm<br>Depth: 149 mm<br>Width: 13.3 "<br>Depth: 5.87 "                |
| Suitable for                       | Enclosure type: AE  |
| Gland plate                        | Size: 4   |
| Protection category IP to EN 60529 | IP66 when mounting in the usual position at the bottom                          |
| Packaging unit                     | 1 pc(s).  |
| Net weight                         | 0.5 kg  |
| Gross weight                       | 0.62 kg   |
| Customs tariff number              | 73079100  |
| ETIM 9                             | EC000211  |
| ETIM 8                             | EC000211  |

# Features

---

ECLASS 8.0

27142421

---

Product description

SZ Metal gland plate, with metric knock-outs, WD: 339x149 mm,  
size: 4