

Rittal – The System.

Faster – better – everywhere.



SZ 2562.400 Metal gland plate

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2562.400 - Metal gland plate

As a spare/replacement part for flange plates supplied loose as standard, protection category IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 2562.400
Version	Solid
Product description	As a spare/replacement part for flange plates supplied loose as standard.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 339 mm Depth: 149 mm Width: 13.3 " Depth: 5.87 "
Suitable for	Enclosure type: AE
Gland plate	Size: 4
Protection category IP to EN 60 529	IP66 when mounting in the usual position at the bottom
Packaging unit	1 pc(s).
Net weight	0.5 kg
Gross weight	0.588 kg
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Metal gland plate, closed, WD: 339x149 mm, size: 4